





LEICA Magnus i

Reticles and subtensions



Reticle 4A


Table with dimensions on page 4






LEICA Magnus i

Reticles and subtensions



Reticle 4A


Table with dimensions on page 4






LEICA Magnus i

Reticles and subtensions



Reticle 4A


Table with dimensions on page 4






LEICA Magnus i

Reticles and subtensions



Reticle 4A


Table with dimensions on page 4






LEICA Magnus i

Reticles and subtensions



Reticle 4A

Table with dimensions on page 4





LEICA Magnus i

Subtensions in cm/100 m

Riflescope		Leica Magnus i 1-6.3x24				
Reticle		4A	3D	CDi	Ballistic	Plex
Bar spacing min.		1400.00	2800.00	320.00	--	509.00
Magnification 10x	A	140.00	--	--	--	--
Magnification max.		222.00	444.00	50.80	--	79.00
Bar spacing min.		700.00	--	--	--	--
Magnification 10x	A/2	70.00	--	--	--	--
Magnification max.		111.00	--	--	--	--
Line thickness min.		5.00	8.00	8.00	--	5.30
Magnification 10x	B	0.50	--	--	--	--
Magnification max.		0.80	1.26	1.26	--	0.80
Bar thickness min.		24.00	--	38.00	--	24.00
Magnification 10x	C	2.40	--	--	--	--
Magnification max.		3.80	--	6.00	--	3.80
Dot diameter min.		24.00	24.00	24.00	--	15.00
Magnification 10x	D	1.50	--	--	--	--
Magnification max.		3.80	3.80	3.80	--	3.80
Bar spacing min.		--	1400.00	20.00	--	--
Magnification 10x	E	--	--	--	--	--
Magnification max.		--	222.00	3.20	--	--
Bar length min.		--	50.00	--	--	--
Magnification 10x	F	--	--	--	--	--
Magnification max.		--	7.90	--	--	--
Bar length min.		--	60.00	--	--	--
Magnification 10x	G	--	--	--	--	--
Magnification max.		--	9.50	--	--	--
Bar spacing min.		--	80.00	--	--	--
Magnification 10x	H	--	--	--	--	--
Magnification max.		--	12.70	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	I	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	J	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	K	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	L	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	M	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	N	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	O	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar thickness min.		--	--	19.00	--	--
Magnification 10x	P	--	--	--	--	--
Magnification max.		--	--	3.00	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	X1	--	--	--	--	--
Magnification max.		--	--	--	--	--

All specifications in centimeters on 100 meters (cm/100m)



LEICA Magnus i

Subtensions in cm/100 m

Riflescope		Leica Magnusi 1-6.3x24				
Reticle		4A	3D	CDi	Ballistic	Plex
Bar spacing min.		--	--	--	--	--
Magnification 10x	X2	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Vergrößerung 10-fach	X3	--	--	--	--	--
Vergrößerung max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Vergrößerung 10-fach	X4	--	--	--	--	--
Vergrößerung max.		--	--	--	--	--
Bar width min.		--	--	--	--	--
Magnification 10x	Y1	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar width min.		--	--	--	--	--
Magnification 10x	Y2	--	--	--	--	--
Magnification max.		--	--	--	--	--
Dot spacing min.		--	--	--	--	--
Magnification 10x	Z1	--	--	--	--	--
Magnification max.		--	--	--	--	--
Dot spacing min.		--	--	--	--	--
Magnification 10x	Z2	--	--	--	--	--
Magnification max.		--	--	--	--	--
Dot spacing min.		--	--	--	--	--
Magnification 10x	Z3	--	--	--	--	--
Magnification max.		--	--	--	--	--
Dot spacing min.		--	--	--	--	--
Magnification 10x	Z4	--	--	--	--	--
Magnification max.		--	--	--	--	--

All specifications in centimeters on 100 meters (cm/100m)



LEICA Magnus i

Subtensions in cm/100 m

Riflescope		Leica Magnus i 1.5-10x42				
Reticle		4A	3D	CDi	Ballistic	Plex
Bar spacing min.		933.00	1866.00	213.00	666.00	333.00
Magnification 10x	A	--	--	--	--	--
Magnification max.		140.00	280.00	32.00	100.00	50.00
Bar spacing min.		467.00	--	--	333.00	--
Magnification 10x	A/2	--	--	--	--	--
Magnification max.		70.00	--	--	50.00	--
Line thickness min.		3.30	5.30	5.30	3.30	3.30
Magnification 10x	B	--	--	--	--	--
Magnification max.		0.50	0.80	0.80	0.50	0.50
Bar thickness min.		16.00	--	25.30	16.00	16.00
Magnification 10x	C	--	--	--	--	--
Magnification max.		2.40	--	3.80	2.40	2.40
Dot diameter min.		10.00	16.00	16.00	10.00	10.00
Magnification 10x	D	--	--	--	--	--
Magnification max.		1.50	2.40	2.40	1.50	1.50
Bar spacing min.		--	933.00	13.30	66.60	--
Magnification 10x	E	--	--	--	--	--
Magnification max.		--	140.00	2.00	10.00	--
Bar length min.		--	33.30	--	66.60	--
Magnification 10x	F	--	--	--	--	--
Magnification max.		--	5.00	--	10.00	--
Bar length min.		--	40.00	--	133.00	--
Magnification 10x	G	--	--	--	--	--
Magnification max.		--	6.00	--	20.00	--
Bar spacing min.		--	53.30	--	100.00	--
Magnification 10x	H	--	--	--	--	--
Magnification max.		--	8.00	--	15.00	--
Bar spacing min.		--	--	--	133.00	--
Magnification 10x	I	--	--	--	--	--
Magnification max.		--	--	--	20.00	--
Bar spacing min.		--	--	--	166.00	--
Magnification 10x	J	--	--	--	--	--
Magnification max.		--	--	--	25.00	--
Bar spacing min.		--	--	--	200.00	--
Magnification 10x	K	--	--	--	--	--
Magnification max.		--	--	--	30.00	--
Bar spacing min.		--	--	--	233.00	--
Magnification 10x	L	--	--	--	--	--
Magnification max.		--	--	--	35.00	--
Bar spacing min.		--	--	--	267.00	--
Magnification 10x	M	--	--	--	--	--
Magnification max.		--	--	--	40.00	--
Bar spacing min.		--	--	--	300.00	--
Magnification 10x	N	--	--	--	--	--
Magnification max.		--	--	--	45.00	--
Bar spacing min.		--	--	--	333.00	--
Magnification 10x	O	--	--	--	--	--
Magnification max.		--	--	--	50.00	--
Bar thickness min.		--	--	12.65	--	--
Magnification 10x	P	--	--	--	--	--
Magnification max.		--	--	1.90	--	--
Bar spacing min.		--	--	--	64.00	--
Magnification 10x	X1	--	--	--	--	--
Magnification max.		--	--	--	10.00	--

All specifications in centimeters on 100 meters (cm/100m)



LEICA Magnus i

Subtensions in cm/100m

Riflescope		Leica Magnusi 1.5-10x42				
Reticle		4A	3D	CDi	Ballistic	Plex
Bar spacing min.		--	--	--	129.00	--
Magnification 10x	X2	--	--	--	--	--
Magnification max.		--	--	--	20.00	--
Bar spacing min.		--	--	--	193.00	--
Vergrößerung 10-fach	X3	--	--	--	--	--
Vergrößerung max.		--	--	--	30.00	--
Bar spacing min.		--	--	--	258.00	--
Vergrößerung 10-fach	X4	--	--	--	--	--
Vergrößerung max.		--	--	--	40.00	--
Bar width min.		--	--	--	64.00	--
Magnification 10x	Y1	--	--	--	--	--
Magnification max.		--	--	--	10.00	--
Bar width min.		--	--	--	129.00	--
Magnification 10x	Y2	--	--	--	--	--
Magnification max.		--	--	--	20.00	--
Dot spacing min.		--	--	--	97.00	--
Magnification 10x	Z1	--	--	--	--	--
Magnification max.		--	--	--	15.00	--
Dot spacing min.		--	--	--	161.00	--
Magnification 10x	Z2	--	--	--	--	--
Magnification max.		--	--	--	25.00	--
Dot spacing min.		--	--	--	226.00	--
Magnification 10x	Z3	--	--	--	--	--
Magnification max.		--	--	--	35.00	--
Dot spacing min.		--	--	--	290.00	--
Magnification 10x	Z4	--	--	--	--	--
Magnification max.		--	--	--	45.00	--

All specifications in centimeters on 100 meters (cm/100m)



LEICA Magnus i

Subtensions in cm/100 m

Riflescope		Leica Magnusi 1.8-12x50				
Reticle		4A	3D	CDi	Ballistic	Plex
Bar spacing min.		770.00	--	--	552.00	278.00
Magnification 10x	A	140.00	--	--	83.00	41.70
Magnification max.		85.33	--	--	100.00	50.00
Bar spacing min.		385.00	--	--	276.00	--
Magnification 10x	A/2	70.00	--	--	41.50	--
Magnification max.		29.17	--	--	50.00	--
Line thickness min.		2.80	--	--	2.80	2.80
Magnification 10x	B	0.50	--	--	0.42	0.42
Magnification max.		0.42	--	--	0.50	0.50
Bar thickness min.		13.00	--	--	13.00	13.30
Magnification 10x	C	2.40	--	--	2.00	2.00
Magnification max.		2.00	--	--	2.40	2.40
Dot diameter min.		8.30	--	--	8.00	8.30
Magnification 10x	D	1.50	--	--	1.30	1.30
Magnification max.		1.30	--	--	1.50	1.50
Bar spacing min.		--	--	--	--	--
Magnification 10x	E	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar length min.		--	--	--	--	--
Magnification 10x	F	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar length min.		--	--	--	--	--
Magnification 10x	G	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	H	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	I	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	J	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	K	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	L	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	M	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	N	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	--	--
Magnification 10x	O	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar thickness min.		--	--	--	--	--
Magnification 10x	P	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	55.00	--
Magnification 10x	X1	--	--	--	8.00	--
Magnification max.		--	--	--	10.00	--

All specifications in centimeters on 100 meters (cm/100m)



LEICA Magnus i

Subtensions in cm/100 m

Riflescope		Leica Magnusi 1.8-12x50				
Reticle		4A	3D	CDi	Ballistic	Plex
Bar spacing min.		--	--	--	110.00	--
Magnification 10x	X2	--	--	--	17.00	--
Magnification max.		--	--	--	20.00	--
Bar spacing min.		--	--	--	165.00	--
Vergrößerung 10-fach	X3	--	--	--	25.00	--
Vergrößerung max.		--	--	--	30.00	--
Bar spacing min.		--	--	--	220.00	--
Vergrößerung 10-fach	X4	--	--	--	33.00	--
Vergrößerung max.		--	--	--	40.00	--
Bar width min.		--	--	--	55.00	--
Magnification 10x	Y1	--	--	--	8.00	--
Magnification max.		--	--	--	10.00	--
Bar width min.		--	--	--	110.00	--
Magnification 10x	Y2	--	--	--	17.00	--
Magnification max.		--	--	--	20.00	--
Dot spacing min.		--	--	--	82.00	--
Magnification 10x	Z1	--	--	--	12.50	--
Magnification max.		--	--	--	15.00	--
Dot spacing min.		--	--	--	138.00	--
Magnification 10x	Z2	--	--	--	21.00	--
Magnification max.		--	--	--	25.00	--
Dot spacing min.		--	--	--	190.00	--
Magnification 10x	Z3	--	--	--	29.00	--
Magnification max.		--	--	--	35.00	--
Dot spacing min.		--	--	--	245.00	--
Magnification 10x	Z4	--	--	--	37.00	--
Magnification max.		--	--	--	45.00	--

All specifications in centimeters on 100 meters (cm/100m)



LEICA Magnus i

Subtensions in cm/100 m

Riflescope		Leica Magnus i 2.4-16x56				
Reticle		4A	3D	CDi	Ballistic	Plex
Bar spacing min.		583.00	--	--	417.00	208.00
Magnification 10x	A	88.00	--	--	62.50	31.50
Magnification max.		140.00	--	--	100.00	50.00
Bar spacing min.		292	--	--	209	--
Magnification 10x	A/2	44.00	--	--	104.50	--
Magnification max.		70.00	--	--	50.00	--
Line thickness min.		2.10	--	--	2.10	2.10
Magnification 10x	B	0.31	--	--	0.31	0.31
Magnification max.		0.50	--	--	0.50	0.50
Bar thickness min.		10.00	--	--	10.00	10.00
Magnification 10x	C	1.50	--	--	1.50	1.50
Magnification max.		2.40	--	--	2.40	2.40
Dot diameter min.		6.30	--	--	6.30	6.30
Magnification 10x	D	1.00	--	--	1.00	0.90
Magnification max.		1.50	--	--	1.50	1.50
Bar spacing min.		--	--	--	41.60	--
Magnification 10x	E	--	--	--	6.30	--
Magnification max.		--	--	--	10.00	--
Bar length min.		--	--	--	41.60	--
Magnification 10x	F	--	--	--	6.30	--
Magnification max.		--	--	--	20.00	--
Bar length min.		--	--	--	83.30	--
Magnification 10x	G	--	--	--	12.50	--
Magnification max.		--	--	--	20.00	--
Bar spacing min.		--	--	--	62.50	--
Magnification 10x	H	--	--	--	9.40	--
Magnification max.		--	--	--	15.00	--
Bar spacing min.		--	--	--	83.30	--
Magnification 10x	I	--	--	--	12.50	--
Magnification max.		--	--	--	25.00	--
Bar spacing min.		--	--	--	104.00	--
Magnification 10x	J	--	--	--	15.60	--
Magnification max.		--	--	--	25.00	--
Bar spacing min.		--	--	--	125.00	--
Magnification 10x	K	--	--	--	18.80	--
Magnification max.		--	--	--	30.00	--
Bar spacing min.		--	--	--	146.00	--
Magnification 10x	L	--	--	--	21.90	--
Magnification max.		--	--	--	35.00	--
Bar spacing min.		--	--	--	166.00	--
Magnification 10x	M	--	--	--	25.00	--
Magnification max.		--	--	--	40.00	--
Bar spacing min.		--	--	--	187.50	--
Magnification 10x	N	--	--	--	28.10	--
Magnification max.		--	--	--	45.00	--
Bar spacing min.		--	--	--	208.00	--
Magnification 10x	O	--	--	--	???	--
Magnification max.		--	--	--	32.00	--
Bar thickness min.		--	--	--	--	--
Magnification 10x	P	--	--	--	--	--
Magnification max.		--	--	--	--	--
Bar spacing min.		--	--	--	41.00	--
Magnification 10x	X1	--	--	--	6.30	--
Magnification max.		--	--	--	10.00	--

All specifications in centimeters on 100 meters (cm/100m)



LEICA Magnus i

Subtensions in cm/100 m

Riflescope		Leica Magnus i 2.4-16x56				
Reticle		4A	3D	CDi	Ballistic	Plex
Bar spacing min.		--	--	--	83.30	--
Magnification 10x	X2	--	--	--	12.50	--
Magnification max.		--	--	--	20.00	--
Bar spacing min.		--	--	--	125.00	--
Vergrößerung 10-fach	X3	--	--	--	18.80	--
Vergrößerung max.		--	--	--	30.00	--
Bar spacing min.		--	--	--	167.00	--
Vergrößerung 10-fach	X4	--	--	--	25.00	--
Vergrößerung max.		--	--	--	40.00	--
Bar width min.		--	--	--	41.70	--
Magnification 10x	Y1	--	--	--	6.30	--
Magnification max.		--	--	--	10.00	--
Bar width min.		--	--	--	83.30	--
Magnification 10x	Y2	--	--	--	12.50	--
Magnification max.		--	--	--	20.00	--
Dot spacing min.		--	--	--	62.50	--
Magnification 10x	Z1	--	--	--	9.40	--
Magnification max.		--	--	--	15.00	--
Dot spacing min.		--	--	--	104.00	--
Magnification 10x	Z2	--	--	--	15.60	--
Magnification max.		--	--	--	25.00	--
Dot spacing min.		--	--	--	146.00	--
Magnification 10x	Z3	--	--	--	21.90	--
Magnification max.		--	--	--	35.00	--
Dot spacing min.		--	--	--	188.00	--
Magnification 10x	Z4	--	--	--	28.10	--
Magnification max.		--	--	--	45.00	--

All specifications in centimeters on 100 meters (cm/100m)